

Eppendorf Certificate

Certificate of Quality

Eppendorf Centrifuges MiniSpin[®], MiniSpin[®] plus, 5418, 5418 R, 5424, 5425, 5424 R, 5427 R, 5430, 5430 R, 5702, 5702 R, 5702 RH, 5804, 5804 R, 5810, 5810 R, 5910 R and 5920 R

Eppendorf Centrifuges are tested in accordance with current manufacturing specifications and safety requirements.

Testing with respect to compliance within the defined limitations and tolerances includes assessment of

- > rotational speed,
- > run time,
- > cooling performance, if applicable.

For Operational Qualification by certified service personnel, documentation including the defined limitations and tolerances is available and can be provided upon request.

The Eppendorf Quality Management System is certified in accordance with the international standards ISO 9001 and ISO 13485.

Hamburg, June 2018

Eppendorf Certificate

Certificate of Quality - Addendum

Eppendorf Centrifuges MiniSpin®, MiniSpin® plus, 5418, 5418 R, 5424, 5425, 5424 R, 5427 R, 5430, 5430 R, 5702, 5702 R, 5702 RH, 5804, 5804 R, 5810, 5810 R, 5910 R and 5920 R

Limitations and tolerances

Eppendorf Centrifuge	Rotor	Rotational Speed	Temperature	Run Time
MiniSpin®	F-45-12-11	13,400 rpm ±402 rpm	ΔT ≤ 14 K	300 s ± 2 s
MiniSpin® plus	F-45-12-11	14,500 rpm ±435 rpm	ΔT ≤ 14 K	300 s ± 2 s
5418	FA-45-18-11	14,000 rpm ±100 rpm	ΔT ≤ 12 K	300 s ± 2 s
5418 R	FA-45-18-11	14,000 rpm ±100 rpm	4 °C ± 2 K	300 s ± 2 s
5424 (100 V / 230 V)	FA-45-24-11	14,680 rpm ±100 rpm	ΔT ≤ 18 K	300 s ± 2 s
5424 (120 V)	FA-45-24-11	15,000 rpm ±100 rpm	ΔT ≤ 18 K	300 s ± 2 s
5425	FA-24x2	15,060 rpm ±40 rpm	ΔT ≤ 17 K	300 s ± 3 s
5424 R	FA-45-24-11	14,680 rpm ±100 rpm	4 °C ± 2 K	300 s ± 2 s
5427 R	F-45-48-11	14,000 rpm ±50 rpm	4 °C ± 2 K	300 s ± 2 s
5427 R	F-45-30-11	14,000 rpm ±50 rpm	4 °C ± 2 K	300 s ± 2 s
5430	FA-45-30-11	14,000 rpm ±100 rpm	ΔT ≤ 14 K	300 s ± 2 s
5430 R	FA-45-30-11	14,000 rpm ±100 rpm	4 °C ± 2 K	300 s ± 2 s
5702	F-35-30-17	4,400 rpm ±44 rpm	ΔT ≤ 12 K	300 s ± 2 s
5702 R	A-4-38	4,400 rpm ±44 rpm	4 °C ± 2 K@4400 rpm	300 s ± 2 s
5702 RH	A-4-38	4,400 rpm ±44 rpm	4 °C ± 2 K@4400 rpm 37 °C ± 2 K@4400 rpm	300 s ± 2 s
5804	A-4-44	5,000 rpm ±50 rpm	ΔT ≤ 13 K	300 s ± 2 s
5804 R	A-4-44	5,000 rpm ±50 rpm	7 °C ± 2 K	300 s ± 2 s
5810	A-4-62	4,000 rpm ±40 rpm	ΔT ≤ 13 K	300 s ± 2 s
5810 R	A-4-62	4,000 rpm ±40 rpm	6 °C ± 2 K	300 s ± 2 s
5810	F-34-6-38	12,000 rpm ±40 rpm	ΔT ≤ 16 K	300 s ± 2 s
5810 R	F-34-6-38	12,000 rpm ±40 rpm	13 °C ± 2 K	300 s ± 2 s
5810	A-4-81	4,000 rpm ±40 rpm	ΔT ≤ 13 K	300 s ± 2 s
5810 R	A-4-81	4,000 rpm ±40 rpm	8 °C ± 2 K	300 s ± 2 s
5910 R	S4xUniversal	14,000 rpm ±40 rpm	4 °C ± 2 K	300 s ± 3 s
5920 R	S4xUniversal-Large	14,000 rpm ±40 rpm	4 °C ± 2 K	300 s ± 3 s

Dr. R. Hashemi
Product Life Cycle Manager

Dr. B. Schreiber
Vice President Quality Management &
Regulatory Affairs

Your local distributor: www.eppendorf.com/contact
Eppendorf AG · 22331 Hamburg · Germany
eppendorf@eppendorf.com

ISO 9001
Certified

ISO 13485
Certified

ISO 14001
Certified